



CA30M Wet Tantalum Capacitor


1, Brief Introduction



2, General Characteristics

| | | | |
|----|------|----|----|
| | °C ~ | °C | °C |
| °C | °C | μ | μ |

3, Drawing , Case Dimension and Max. weight:



| | () | () | |
|--|-----|-----|--|
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |



Shanghai Green Tech Co.,Ltd.

| | | | (μ) | °C | °C | °C | () | °C |
|--|--|--|------|----|----|----|-----|----|
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |



| | | | (μ) | $^{\circ}\text{C}$ | $^{\circ}\text{C}$ | $^{\circ}\text{C}$ | () $^{\circ}\text{C}$ |
|--|--|--|-----------|--------------------|--------------------|--------------------|---------------------------|
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |



| | | | | | | | |
|--|--|--|-----------|----|----|----|---|
| | | | (μ) | °C | °C | °C | F |
|--|--|--|-----------|----|----|----|---|



5, How to order

(GTC A30M-105M0160)

| | | | | | |
|----|-------|-----|---|-----|---|
| GT | CA30M | 105 | M | 016 | 0 |
|----|-------|-----|---|-----|---|

Notes:

- ,
- ,
- ,
- ,

°C